

Fence Clamp, Three Conductor



The nVent ERICO Fence Clamp, Three Conductor, is designed to provide a reliable and efficient grounding solution for various applications. Manufactured from copper alloy, this clamp ensures maximum conductivity and durability. It features a multi-functional body design that allows for clamping parallel cables or wires to a pipe or rod in a perpendicular orientation and clamping three equal-sized cables to a metal pipe, rod, or post. Furnished with silicon bronze or stainless steel U-bolt, nut, and lock washer, this clamp is suitable for direct burial in earth or concrete, making it a versatile and dependable choice for grounding and bonding applications.

FEATURES

Theft-deterrent appearance

Silicon bronze or stainless steel hardware included

Copper alloy minimizes the risk of corrosion

Multi-functional body design

SPECIFICATIONS

Finish: Bare
Material: Bronze

Table 1/1

Catalog Number	Conductor Size	Complies With
GR-4	#4 Stranded - #8 Stranded	UL® 467
GR-5	2/0 Stranded - 4/0 Stranded	UL® 467
GR-6	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-7	500 kcmil - 300 kcmil	
GR-10	250 kcmil Stranded - 2/0 Stranded, 2/0 Stranded	UL® 467

Catalog Number	Conductor Size	Complies With
GR-11	500 kcmil - 300 kcmil	
GR-9	2/0 Stranded - 4/0 Stranded	UL® 467
GR-14	2/0 Stranded - 4/0 Stranded	UL® 467
GR-15	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-16	500 kcmil - 300 kcmil	
GR-20	2/0 Stranded - 4/0 Stranded	UL® 467
GR-21	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-26	2/0 Stranded - 4/0 Stranded	UL® 467
GR-27	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-31	#4 Stranded - #8 Stranded	UL® 467
GR-32	2/0 Stranded - 4/0 Stranded	UL® 467
GR-33	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-38	2/0 Stranded - 4/0 Stranded	UL® 467
GR-44	2/0 Stranded - 4/0 Stranded	UL® 467
GR-50	2/0 Stranded - 4/0 Stranded	UL® 467
GR-61	2/0 Stranded - 4/0 Stranded	UL® 467
GR-39	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-45	250 kcmil Stranded - 2/0 Stranded	UL® 467

Catalog Number	Conductor Size	Complies With
GR-62	250 kcmil Stranded - 2/0 Stranded	UL® 467

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE