

Joint Bond Mold Only, Power



FEATURES

Replacement mold designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

SPECIFICATIONS

Bond Terminal Style: C

Material: Graphite

Table 1/1

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Orientation
MRR50D	UIC54, UIC60	50 mm ² Stranded	9.27mm	Left Hand
MRR50G	UIC54, UIC60	50 mm ² Stranded	9.27mm	Right Hand
PBCS6CWPRHM	85 lb to 141 lb T-Rail Sections	3/0 Composite	14.53mm	Right Hand
PBCS6CWPLHM	85 lb to 141 lb T-Rail Sections	3/0 Composite	14.53mm	Left Hand
PBC2WRHM	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	Right Hand
PBC2WLHM	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	Left Hand

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE