


nVent ERICO PermaGround Intersystem Ground Tap



nVent ERICO PermaGround Lay-in Intersystem Ground Tap allows for fast and simple installation on a ground conductor below the meter. The lay-in style eliminates the need to cut or splice into existing conductors, and with no mounting required. The tap is dual-rated for use with both copper and aluminum conductors.

CERTIFICATIONS



FEATURES

Lay in style, eliminates the need to cut or splice into existing conductor

No mounting required, allows fast simple installation on ground conductor below meter

Dual-rated for use with copper and aluminum conductors

SPECIFICATIONS


Material: Aluminum

Table 1/1

Catalog Number	Conductor Material	Direct Burial	Height (H)	Length (L)	Width (W)	Unit Weight
GBT-1/0	Copper, Aluminum	No	29.464mm	57.15mm	28.575mm	0.1 kg
GBT-1/0-M	Copper, Aluminum	No	29.464mm	57.15mm	44.45mm	0.11 kg

CatalogNumber	Conductor Material	Direct Burial	Height (H)	Length (L)	Width (W)	Unit Weight
GBT-1/0-M-W/C	Copper, Aluminum	No	56.997mm	99.618mm	74.295mm	0.15 kg
GBT-250	Copper, Aluminum	No	40.309mm	57.15mm	34.925mm	0.18 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE