

APO Non-Metallic Hinges

APO Non-Metallic Hinges allow conversion of APO enclosure screw cover to a hinged cover.



FEATURES

To attach hinges, holes must be drilled in the cover and the base

Templates are provided for proper placement

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Color	Color Code	Quick Ship
10000.005LG	10000.005LG	Polyamide	Smooth Matte	Light Gray	RAL 7035	No
10000.091LG	10000.091LG	Polyamide	Smooth Matte	Light Gray	RAL 7035	No
10000.086LG	10000.086LG	Polyamide	Smooth Matte	Light Gray	RAL 7035	No
10000.089LG	10000.089LG	Polyamide	Smooth Matte	Light Gray	RAL 7035	No
10000.087LG	10000.087LG	Polyamide	Smooth Matte	Light Gray	RAL 7035	No
10000.088LG	10000.088LG	Polyamide	Smooth Matte	Light Gray	RAL 7035	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE