

APO DT Trnsp Hngd Scr Cvr Insp Wdw Blk Insrt, 19.20x11.89x1.77, Smooth, Fiberglass

CATALOG NUMBER

A51-DTCOVERKIT



APO DT Covers are designed for use as inspection windows in highly corrosive environments where easy viewing and access is essential.

INDUSTRY STANDARDS

UL Listed Types 3, 3R, 4, 4X, 13

FEATURES

Available sized from 12" x 7" to 24" x 12" (H x W)

DT Covers are maintenance free and corrosion resistant

Frames are made from hot compression molded halogen free, self extinguishing fiberglass reinforced polyester (FRP) that can withstand continuous temperatures from -58°F to 302°F (-50°C to 150°C)

Inspection windows are made from transparent polycarbonate that can withstand continuous temperatures to 248°F (120°C)

Included thumb screw inserts allow quick window opening for access to interior component

Gaskets are made from continuously poured polyurethane foam

PRODUCT ATTRIBUTES

Article Number: A51-DTCOVERKIT

Height: 488mm

Width: 302mm

Depth: 45mm

Material: Fiberglass

Finish: Smooth Matte

Color: Light Gray

Color Code: RAL 7035

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE