nVent | HOFFMAN

We connect and protect

Ventilated Bottom Plate, CVB, 23x800x600mm, Galvanized, Mild steel

CATALOG NUMBER

CVB0806

Can be used in combination with a ventilated plinth PV. 33% ventilated.

FEATURES

Description: Can be used in combination with a ventilated plinth PV. 33% ventilated.

Material: 1.5 mm perforated zinc plated steel.

Pack quantity: 3 pieces, 4 pieces for D>600mm, with mounting material.

Mounting requirements: Use in combination with ventilated plinths PV.

PRODUCT ATTRIBUTES

Article Number: CVB0806

Height: 23mm

Width: 800mm

Depth: 600mm

Enclosure Material: Mild Steel; Galvanized Steel

Product Family: Free-Standing

Material: Mild Steel

Finish: Galvanized

Thickness: 1.5mm

Package Quantity: 4

Weight: 3kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.