

Frameless Window Kit



Designed for use on many Type 12 and 13 enclosures. These kits are for indoor use in a temperature range of 55 F to 125 F (13 C to 52 C). For more severe conditions, use Steel, Stainless Steel, or Non-Metallic Window Kits. The window is scratch-resistant. Special high-strength, double-sided tape is supplied as well as screw fasteners. Windows can be cut to smaller sizes.

FEATURES

For indoor use only

Allow .50-inch (13-mm) overlap on each side of window for tape

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Thickness	Window Size	Cutout Size
APWKE96	57630	Polycarbonate	Transparent	3mm	244 x 183mm	219 x 157mm
APWKE133	57620	Polycarbonate	Transparent	3mm	353 x 99mm	327 x 73mm
APWKE52	57610	Polycarbonate	Transparent	3mm	140 x 76mm	114 x 51mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE