

Full Subpanel



ProLine subpanels are designed to provide maximum panel depth, panel size and ease of installation. Full subpanels slide into the frame on nylon glide blocks, which support the entire weight of the subpanel.

Additional Mounting Hardware (catalog number PMKPF) is available for applications requiring more support in the center or bottom of the subpanel. This is required if the enclosure will be tipped in transit or if the panel is not located at the bottom of the enclosure on the glide blocks. In addition, 3-row grid straps are required for installation unless the panel is in the rearmost position.

FEATURES

All necessary mounting hardware is included

Subpanels have flanges on all sides

Subpanels can be mounted at nearly any depth in 25-mm increments

Panels installed in the rearmost position in joined (ganged) enclosures provide a continuous mounting surface without requiring joining panels

Mounting hardware attaches to the top or to the sides of the frame

Subpanels are 12 gauge (2.5 mm); Double-bay subpanels are 11 gauge (3.0 mm) for all frames 1400mm in height or greater

Subpanels are available standard in either conductive or white painted finish

Additional Mounting Hardware (PMKPF) for securing panel to frame in the center of the subpanel is sold separately

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Color	Finish	Thickness	Quick Ship
PPF146	98960	Mild Steel	White	Powder Coated	2.66mm	No
PPF146G	26239	Mild Steel		Galvanized	2.66mm	No
PPF148	98970	Mild Steel	White	Powder Coated	2.66mm	No
PPF148G	26249	Mild Steel		Galvanized	2.66mm	No
PPF166	98990	Mild Steel	White	Powder Coated	2.66mm	No
PPF166G	26259	Mild Steel		Galvanized	2.66mm	No
PPF168	99010	Mild Steel	White	Powder Coated	2.66mm	No
PPF168G	26279	Mild Steel		Galvanized	2.66mm	No
PPF1810G	26319	Mild Steel		Galvanized	2.66mm	No
PPF1810	99060	Mild Steel	White	Powder Coated	2.66mm	No
PPF186	99030	Mild Steel	White	Powder Coated	2.66mm	No
PPF186G	26289	Mild Steel		Galvanized	2.66mm	No
PPF188	99050	Mild Steel	White	Powder Coated	2.66mm	No
PPF188G	26309	Mild Steel		Galvanized	2.66mm	No
PPF2010	99120	Mild Steel	White	Powder Coated	2.66mm	No
PPF2010G	26369	Mild Steel		Galvanized	2.66mm	No
PPF204	25639	Mild Steel	White	Powder Coated	2.66mm	No
PPF206	99090	Mild Steel	White	Powder Coated	2.66mm	No
PPF206G	26339	Mild Steel		Galvanized	2.66mm	No

Catalog Number	Article Number	Material	Color	Finish	Thickness	Quick Ship
PPF207	99100	Mild Steel	White	Powder Coated	2.66mm	No
PPF207G	26349	Mild Steel		Galvanized	2.66mm	No
PPF208	99110	Mild Steel	White	Powder Coated	2.66mm	No
PPF208G	26359	Mild Steel		Galvanized	2.66mm	No
PPF2210G	26419	Mild Steel		Galvanized	2.66mm	No
PPF2210	99180	Mild Steel	White	Powder Coated	2.66mm	No
PPF226G	26389	Mild Steel		Galvanized	2.66mm	No
PPF226	99150	Mild Steel	White	Powder Coated	2.66mm	No
PPF227	99160	Mild Steel	White	Powder Coated	2.66mm	No
PPF227G	26399	Mild Steel		Galvanized	2.66mm	No
PPF228	99170	Mild Steel	White	Powder Coated	2.66mm	No
PPF228G	26409	Mild Steel		Galvanized	2.66mm	No
PPF76	98930	Mild Steel	White	Powder Coated	2.66mm	No
PPF76G	26219	Mild Steel		Galvanized	2.66mm	No
PPF78	98940	Mild Steel	White	Powder Coated	2.66mm	No
PPF78G	26229	Mild Steel	White	Galvanized	2.66mm	No
PPF1212G	29845	Mild Steel		Galvanized	2.66mm	No
PPF126G	29842	Mild Steel		Galvanized	2.66mm	No
PPF128G	29843	Mild Steel		Galvanized	2.66mm	No
PPF184G	29844	Mild Steel		Galvanized	2.66mm	No

Catalog Number	Article Number	Material	Color	Finish	Thickness	Quick Ship
PPF204G2	29904	Mild Steel		Galvanized	2.66mm	No
PPF1412	98980	Mild Steel	White	Powder Coated	3.04mm	No
PPF1612	99020	Mild Steel	White	Powder Coated	3.04mm	No
PPF1612G	14266	Mild Steel		Galvanized	3.04mm	No
PPF1812	99070	Mild Steel	White	Powder Coated	3.04mm	No
PPF1812G	14267	Mild Steel		Galvanized	3.04mm	No
PPF1816	99080	Mild Steel	White	Powder Coated	3.04mm	No
PPF1816G	14268	Mild Steel		Galvanized	3.04mm	No
PPF1818G	29846	Mild Steel		Galvanized	3.04mm	No
PPF2012	99130	Mild Steel	White	Powder Coated	3.04mm	No
PPF2012G	14271	Mild Steel		Galvanized	3.04mm	No
PPF2016	99140	Mild Steel	White	Powder Coated	3.04mm	No
PPF2016G	14272	Mild Steel		Galvanized	3.04mm	No
PPF2018G2	29891	Mild Steel		Galvanized	3.04mm	No
PPF2212	99190	Mild Steel	White	Powder Coated	3.04mm	No
PPF2212G	14273	Mild Steel		Galvanized	3.04mm	No
PPF712	98950	Mild Steel	White	Powder Coated	3.04mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE