

ProLine G2 Plinth Base



ProLine G2 Plinth Bases install under an enclosure to provide space for cables to enter from below.

FEATURES

Four access panels for cable management options at the base of the enclosure

Sturdy cast aluminum corner supports for superior performance under load

Corner blocks can be installed onto the base of the frame independent of the cover plates, enabling the cover plates to be attached after integration and just prior to shipment

Stackable up to 400mm in height using Plinth Base Stacking Kit (not included)

100 mm or 200 mm options

To maintain a NEMA Type 12 environmental rating, gland plate must also be used in the base of the enclosure

Installation hardware included

SPECIFICATIONS

Thickness: 1.52mm
Color: Jet Black
Finish: Powder Coated
Color Code: RAL 9005

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Quick Ship
P2BP1104	31066	100mm	999mm	364mm	Mild Steel	No
P2BP1105	31067	100mm	999mm	464mm	Mild Steel	No
P2BP1106	31071	100mm	999mm	564mm	Mild Steel	No
P2BP1108	31072	100mm	999mm	764mm	Mild Steel	No
P2BP1124	31073	100mm	1199mm	364mm	Mild Steel	No
P2BP1125	31074	100mm	1199mm	464mm	Mild Steel	No
P2BP1126	31075	100mm	1199mm	564mm	Mild Steel	Yes
P2BP1128	31076	100mm	1199mm	764mm	Mild Steel	No
P2BP1164	31077	100mm	1599mm	364mm	Mild Steel	No
P2BP1165	31078	100mm	1599mm	464mm	Mild Steel	Yes
P2BP1166	31081	100mm	1599mm	564mm	Mild Steel	Yes
P2BP1168	31082	100mm	1599mm	764mm	Mild Steel	No
P2BP1184	34072	100mm	1799mm	364mm	Mild Steel	No
P2BP1185	31083	100mm	1799mm	464mm	Mild Steel	No
P2BP1186	31084	100mm	1799mm	564mm	Mild Steel	Yes
P2BP1188	31085	100mm	1799mm	764mm	Mild Steel	No

Catalog Number	Article Number	Height	Width	Depth	Material	Quick Ship
P2BP145	31086	100mm	399mm	464mm	Mild Steel	No
P2BP146	31087	100mm	399mm	564mm	Mild Steel	No
P2BP164	31088	100mm	599mm	364mm	Mild Steel	No
P2BP165	31091	100mm	599mm	464mm	Mild Steel	No
P2BP166	31093	100mm	599mm	564mm	Mild Steel	No
P2BP168	31094	100mm	599mm	764mm	Mild Steel	No
P2BP1810	31095	100mm	799mm	964mm	Mild Steel	No
P2BP184	31096	100mm	799mm	364mm	Mild Steel	No
P2BP185	31097	100mm	799mm	464mm	Mild Steel	No
P2BP186	31101	100mm	799mm	564mm	Mild Steel	No
P2BP188	31102	100mm	799mm	764mm	Mild Steel	Yes
P2BP2104	31112	193mm	999mm	364mm	Mild Steel	No
P2BP2105	31113	193mm	999mm	464mm	Mild Steel	No
P2BP2106	31115	193mm	999mm	564mm	Mild Steel	No
P2BP2108	31116	193mm	999mm	764mm	Mild Steel	No
P2BP2124	31117	193mm	1199mm	364mm	Mild Steel	No
P2BP2125	31118	193mm	1199mm	464mm	Mild Steel	No
P2BP2126	31121	193mm	1199mm	564mm	Mild Steel	No
P2BP2128	31122	193mm	1199mm	764mm	Mild Steel	No
P2BP2164	31123	193mm	1599mm	364mm	Mild Steel	No

Catalog Number	Article Number	Height	Width	Depth	Material	Quick Ship
P2BP2165	31124	193mm	1599mm	464mm	Mild Steel	No
P2BP2166	31125	193mm	1599mm	564mm	Mild Steel	No
P2BP2168	31126	193mm	1599mm	764mm	Mild Steel	No
P2BP2184	34067	193mm	1799mm	364mm	Mild Steel	No
P2BP2185	31127	193mm	1799mm	464mm	Mild Steel	No
P2BP2186	31128	193mm	1799mm	564mm	Mild Steel	No
P2BP2188	31131	193mm	1799mm	764mm	Mild Steel	No
P2BP245	31132	193mm	399mm	464mm	Mild Steel	No
P2BP246	31133	193mm	399mm	564mm	Mild Steel	No
P2BP264	31134	193mm	599mm	364mm	Mild Steel	No
P2BP265	31135	193mm	599mm	464mm	Mild Steel	No
P2BP266	31137	193mm	599mm	564mm	Mild Steel	No
P2BP268	31138	193mm	599mm	764mm	Mild Steel	No
P2BP2810	31141	193mm	999mm	964mm	Mild Steel	No
P2BP284	31142	193mm	799mm	364mm	Mild Steel	No
P2BP285	31143	193mm	799mm	464mm	Mild Steel	No
P2BP286	31145	193mm	799mm	564mm	Mild Steel	Yes
P2BP288	31146	193mm	799mm	764mm	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE