

ProLine G2 Solid Cover (Front or Rear)



ProLine G2 Solid Sides enclose the open sides of the modular enclosure frame and have innovative design elements incorporated to ensure fast installation and enhanced structural support.

FEATURES

Hinge hanger on top for easy alignment

Formed steel hems on the sides of the covers for enhanced structural support and to protect user from sharp edges

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Attach to enclosure frame with low-profile, flat head screws

Door can be reversed without removing the side covers

Used on the sides of the ProLine G2 frame

Not suitable as a barrier between enclosures (instead use the ProLine G2 barrier panel)

Two grounding studs

All mounting hardware included

Solid Covers are finished with paint over plated surfaces

SPECIFICATIONS

Color: Light Gray

Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2C1012	34774	983mm	1198mm	20mm	Mild Steel	Powder Coated
P2C106	31188	983mm	598mm	20mm	Mild Steel	Powder Coated
P2C108	31191	983mm	798mm	20mm	Mild Steel	Powder Coated
P2C1212	34771	1183mm	1198mm	20mm	Mild Steel	Powder Coated
P2C126	31192	1183mm	598mm	20mm	Mild Steel	Powder Coated
P2C128	31193	1183mm	798mm	20mm	Mild Steel	Powder Coated
P2C1412	34768	1383mm	1198mm	20mm	Mild Steel	Powder Coated
P2C146	31195	1383mm	598mm	20mm	Mild Steel	Powder Coated
P2C146HF	31194	1383mm	598mm	20mm	Mild Steel	Galvanized, Powder Coated
P2C1610	32953	1583mm	998mm	20mm	Mild Steel	Powder Coated
P2C1612	34766	1583mm	1198mm	20mm	Mild Steel	Powder Coated
P2C165	32935	1583mm	498mm	20mm	Mild Steel	Powder Coated
P2C166	31197	1583mm	598mm	20mm	Mild Steel	Powder Coated
P2C167	32936	1583mm	698mm	20mm	Mild Steel	Powder Coated
P2C168	31198	1583mm	798mm	20mm	Mild Steel	Powder Coated
P2C169	32937	1583mm	898mm	20mm	Mild Steel	Powder Coated
P2C1810	31202	1783mm	998mm	20mm	Mild Steel	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2C1810HF	31201	1783mm	998mm	20mm	Mild Steel	Galvanized, Powder Coated
P2C184	31203	1783mm	398mm	20mm	Mild Steel	Powder Coated
P2C185	32938	1783mm	498mm	20mm	Mild Steel	Powder Coated
P2C186	31204	1783mm	598mm	20mm	Mild Steel	Powder Coated
P2C186HF	32954	1783mm	598mm	20mm	Mild Steel	Galvanized, Powder Coated
P2C188	31205	1783mm	798mm	20mm	Mild Steel	Powder Coated
P2C189	32943	1783mm	898mm	20mm	Mild Steel	Powder Coated
P2C2010	31206	1983mm	998mm	20mm	Mild Steel	Powder Coated
P2C2012	34762	1983mm	1198mm	20mm	Mild Steel	Powder Coated
P2C204	31207	1983mm	398mm	20mm	Mild Steel	Powder Coated
P2C205	32944	1983mm	498mm	20mm	Mild Steel	Powder Coated
P2C206	31211	1983mm	598mm	20mm	Mild Steel	Powder Coated
P2C206HF	31208	1983mm	598mm	20mm	Mild Steel	Galvanized, Powder Coated
P2C208	31213	1983mm	798mm	20mm	Mild Steel	Powder Coated
P2C208HF	31212	1983mm	798mm	20mm	Mild Steel	Galvanized, Powder Coated
P2C2210	31214	2183mm	998mm	20mm	Mild Steel	Powder Coated
P2C2212	34757	2183mm	1198mm	20mm	Mild Steel	Powder Coated
P2C225	32947	2183mm	498mm	20mm	Mild Steel	Powder Coated
P2C226	31215	2183mm	598mm	20mm	Mild Steel	Powder Coated
P2C226HF	32955	2183mm	598mm	20mm	Mild Steel	Galvanized, Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
P2C228	31216	2183mm	798mm	20mm	Mild Steel	Powder Coated
P2C228HF	32956	2183mm	798mm	20mm	Mild Steel	Galvanized, Powder Coated
P2C64	31217	583mm	398mm	20mm	Mild Steel	Powder Coated
P2C66	31218	583mm	598mm	20mm	Mild Steel	Powder Coated
P2C68	31221	583mm	789mm	20mm	Mild Steel	Powder Coated
P2C86	31222	783mm	598mm	20mm	Mild Steel	Powder Coated
P2C88	31223	783mm	798mm	20mm	Mild Steel	Powder Coated
P2C148	31196				Mild Steel	Powder Coated
P2C187	32942				Mild Steel	Powder Coated
P2C207	32945				Mild Steel	Powder Coated
P2C227	32948				Mild Steel	Powder Coated
P2C1812	34764				Mild Steel	Powder Coated
P2C209	32946				Mild Steel	Powder Coated
P2C229	32952				Mild Steel	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE