

## ProLine Solid Door



Solid Doors include a removable door bar system on doors taller than 700 mm and wider than 400 mm. Hinge side is reversible. A flush bezel latch operates the 3-point latching system. Doors for 700-mm frames have 2-point latching. Hidden hinges (130-degree swing) permit attachment to the front or back of each enclosure frame. The use of a side-door adapter or a cable entry cabinet allows doors to be attached to the sides of the enclosure frame.

### FEATURES

---

EMC doors are finished with paint over plated surfaces

Optional data pockets, door stops, grounding kits and 180-degree hinges are available

Hinges have easy slide retained hinge pins

Door gasket is foam-in-place urethane to provide a resilient, seamless seal

Two grounding studs are furnished. All mounting hardware is included

## SPECIFICATIONS

**Color:** Light Gray

**Color Code:** RAL 7035

Table 1/1

| Catalog Number | Article Number | Material   | Thickness | Dimensions   | Fits Frame   | Door Type |
|----------------|----------------|------------|-----------|--------------|--------------|-----------|
| PDS126         | 29822          | Mild Steel | 1.52mm    | 1139 x 592mm | 1200 x 600mm | Steel     |
| PDS146         | 94860          | Mild Steel | 1.52mm    | 1339 x 592mm | 1400 x 600mm | Steel     |
| PDS146HF2      | 13489          | Mild Steel | 1.52mm    | 1339 x 592mm | 1400 x 600mm | EMC       |
| PDS165         | 35019          | Mild Steel | 1.52mm    | 1539 x 492mm | 1600 x 500mm | Steel     |
| PDS166         | 94880          | Mild Steel | 1.52mm    | 1539 x 592mm | 1600 x 600mm | Steel     |
| PDS184         | 29824          | Mild Steel | 1.52mm    | 1739 x 392mm | 1800 x 400mm | Steel     |
| PDS185         | 35029          | Mild Steel | 1.52mm    | 1739 x 492mm | 1800 x 500mm | Steel     |
| PDS186         | 94910          | Mild Steel | 1.52mm    | 1739 x 592mm | 1800 x 600mm | Steel     |
| PDS186HF2      | 13539          | Mild Steel | 1.52mm    | 1739 x 592mm | 1800 x 600mm | EMC       |
| PDS204         | 25429          | Mild Steel | 1.52mm    | 1939 x 392mm | 2000 x 400mm | Steel     |
| PDS205         | 35039          | Mild Steel | 1.52mm    | 1939 x 492mm | 2000 x 500mm | Steel     |
| PDS206         | 94950          | Mild Steel | 1.52mm    | 1939 x 592mm | 2000 x 600mm | Steel     |
| PDS206HF2      | 13579          | Mild Steel | 1.52mm    | 1939 x 592mm | 2000 x 600mm | EMC       |
| PDS207         | 94960          | Mild Steel | 1.52mm    | 1939 x 692mm | 2000 x 700mm | Steel     |
| PDS207HF2      | 13589          | Mild Steel | 1.52mm    | 1939 x 692mm | 2000 x 700mm | EMC       |
| PDS225         | 35049          | Mild Steel | 1.52mm    | 2139 x 492mm | 2200 x 500mm | Steel     |
| PDS226         | 94990          | Mild Steel | 1.52mm    | 2139 x 592mm | 2200 x 600mm | Steel     |

| Catalog Number | Article Number | Material   | Thickness | Dimensions   | Fits Frame    | Door Type |
|----------------|----------------|------------|-----------|--------------|---------------|-----------|
| PDS227         | 95000          | Mild Steel | 1.52mm    | 2139 x 692mm | 2200 x 700mm  | Steel     |
| PDS227HF2      | 13629          | Mild Steel | 1.52mm    | 2139 x 692mm | 2200 x 700mm  | EMC       |
| PDS76R         | 94840          | Mild Steel | 1.52mm    | 639 x 592mm  | 700 x 600mm   | Steel     |
| PDS128         | 29823          | Mild Steel | 1.9mm     | 1139 x 792mm | 1200 x 800mm  | Steel     |
| PDS148         | 94870          | Mild Steel | 1.9mm     | 1339 x 792mm | 1400 x 800mm  | Steel     |
| PDS148HF2      | 13499          | Mild Steel | 1.9mm     | 1339 x 792mm | 1400 x 800mm  | EMC       |
| PDS168         | 94900          | Mild Steel | 1.9mm     | 1539 x 792mm | 1600 x 800mm  | Steel     |
| PDS1810        | 94940          | Mild Steel | 1.9mm     | 1739 x 992mm | 1800 x 1000mm | Steel     |
| PDS1810HF2     | 13569          | Mild Steel | 1.9mm     | 1739 x 992mm | 1800 x 1000mm | EMC       |
| PDS188         | 94930          | Mild Steel | 1.9mm     | 1739 x 792mm | 1800 x 800mm  | Steel     |
| PDS188HF2      | 13559          | Mild Steel | 1.9mm     | 1739 x 792mm | 1800 x 800mm  | EMC       |
| PDS2010        | 94980          | Mild Steel | 1.9mm     | 1939 x 992mm | 2000 x 1000mm | Steel     |
| PDS2010HF2     | 13609          | Mild Steel | 1.9mm     | 1939 x 992mm | 2000 x 1000mm | EMC       |
| PDS208         | 94970          | Mild Steel | 1.9mm     | 1939 x 792mm | 2000 x 800mm  | Steel     |
| PDS208HF2      | 13599          | Mild Steel | 1.9mm     | 1939 x 792mm | 2000 x 800mm  | EMC       |
| PDS2210        | 95020          | Mild Steel | 1.9mm     | 2139 x 992mm | 2200 x 1000mm | Steel     |
| PDS228         | 95010          | Mild Steel | 1.9mm     | 2139 x 792mm | 2200 x 800mm  | Steel     |
| PDS78R         | 94850          | Mild Steel | 1.9mm     | 639 x 792mm  | 700 x 800mm   | Steel     |
| PDS78RHF2      | 13479          | Mild Steel | 1.9mm     | 639 x 792mm  | 700 x 800mm   | EMC       |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**