

ProLine Window Doors



Window Doors can be used on the front or rear of ProLine frames to provide viewing of electronic equipment. ProLine Window Doors are designed around a mild steel profile. They have 140-degree hidden hinges and a flush bezel latch that operates a 3-point latching mechanism (doors for 700-mm frames have 2-point latching). Doors have either a smoke-gray tinted polycarbonate or a clear safety glass window; 180-degree hinges are available (order separately).

FEATURES

Install easily on front or rear of enclosure frame; can be hinged on left or right

Have two grounding brackets

Have a .25-in.-thick window that provides maximum protection and viewing area

Have foam-in-place urethane gaskets for door and window to provide optimum sealing

SPECIFICATIONS

Thickness: 1.9mm

Table 1/1

Catalog Number	Article Number	Material	Window Size	Fits Frame	Window Door Type	Safety Glass
PDW146	90960	Mild Steel	1218 x 446mm	1400 x 600mm	Mild Steel, Polycarbonate	1339 x 593mm
PDW148	90970	Mild Steel	1218 x 646mm	1400 x 800mm	Mild Steel, Polycarbonate	1339 x 793mm
PDW166	90980	Mild Steel	1418 x 446mm	1600 x 600mm	Mild Steel, Polycarbonate	1539 x 593mm
PDW186	91010	Mild Steel	1618 x 446mm	1800 x 600mm	Mild Steel, Polycarbonate	1739 x 593mm
PDW188	91030	Mild Steel	1618 x 646mm	1800 x 800mm	Mild Steel, Polycarbonate	1739 x 793mm
PDW206	91040	Mild Steel	1818 x 446mm	2000 x 600mm	Mild Steel, Polycarbonate	1939 x 593mm
PDW207	91050	Mild Steel	1818 x 546mm	2000 x 700mm	Mild Steel, Polycarbonate	1939 x 693mm
PDW208	91060	Mild Steel	1818 x 646mm	2000 x 800mm	Mild Steel, Polycarbonate	1939 x 793mm
PDW226	91070	Mild Steel	2018 x 446mm	2200 x 600mm	Mild Steel, Polycarbonate	2139 x 593mm
PDW227	91080	Mild Steel	2018 x 546mm	2200 x 700mm	Mild Steel, Polycarbonate	2139 x 693mm
PDW228	91090	Mild Steel	2018 x 646mm	2200 x 800mm	Mild Steel, Polycarbonate	2139 x 793mm
PDW76	90940	Mild Steel	518 x 446mm	700 x 600mm	Mild Steel, Polycarbonate	639 x 593mm
PDW78	90950	Mild Steel	518 x 646mm	700 x 800mm	Mild Steel, Polycarbonate	639 x 793mm
PDWG146	90800	Mild Steel	1218 x 446mm	1400 x 600mm	Mild Steel, Safety Glass	1339 x 593mm
PDWG148	90810	Mild Steel	1218 x 646mm	1400 x 800mm	Mild Steel, Safety Glass	1339 x 793mm
PDWG166	90820	Mild Steel	1418 x 446mm	1600 x 600mm	Mild Steel, Safety Glass	1539 x 593mm
PDWG168	15179	Mild Steel	1418 x 646mm	1600 x 800mm	Mild Steel, Safety Glass	1539 x 793mm
PDWG186	15189	Mild Steel	1618 x 446mm	1800 x 600mm	Mild Steel, Safety Glass	1739 x 593mm

Catalog Number	Article Number	Material	Window Size	Fits Frame	Window Door Type	Safety Glass
PDWG188	90870	Mild Steel	1618 x 646mm	1800 x 800mm	Mild Steel, Safety Glass	1739 x 793mm
PDWG206	90880	Mild Steel	1818 x 446mm	2000 x 600mm	Mild Steel, Safety Glass	1939 x 593mm
PDWG207	90890	Mild Steel	1818 x 546mm	2000 x 700mm	Mild Steel, Safety Glass	1939 x 693mm
PDWG208	90900	Mild Steel	1818 x 646mm	2000 x 800mm	Mild Steel, Safety Glass	1939 x 793mm
PDWG226	90910	Mild Steel	2018 x 446mm	2200 x 600mm	Mild Steel, Safety Glass	2139 x 593mm
PDWG228	90930	Mild Steel	2018 x 646mm	2200 x 800mm	Mild Steel, Safety Glass	2139 x 793mm
PDWG76	90780	Mild Steel	518 x 446mm	700 x 600mm	Mild Steel, Safety Glass	639 x 593mm
PDWG78	90790	Mild Steel	518 x 646mm	700 x 800mm	Mild Steel, Safety Glass	639 x 793mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE