

Straight Tube Section Feed-Through Fiberglass



Feed-Through Fiberglass Hinged-Cover, Type 12, 3R
Straight Tube Sections are used for enclosing wire and cable in wireway runs. The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications. Tubes are available in lengths from 12 inch to 120 inch.

FEATURES

Feed-Through Fiberglass Hinged-Cover, Type 12, 3R Straight Tube Sections are used for enclosing wire and cable in wireway runs

The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications

Tubes are available in lengths from 12 inch to 120 inch

SPECIFICATIONS

Color Code: ANSI 61
Material: Fiberglass
Color: Gray
Finish: Smooth Matte

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Depth	Thickness
F44W120STFG	19150	Straight Section	102mm	102mm	3048mm	3.2mm
F44W12STFG	19100	Straight Section	102mm	102mm	305mm	3.2mm
F44W24STFG	19110	Straight Section	102mm	102mm	610mm	3.2mm
F44W36STFG	19120	Straight Section	102mm	102mm	914mm	3.2mm
F44W48STFG	19130	Straight Section	102mm	102mm	1219mm	3.2mm
F44W60STFG	19140	Straight Section	102mm	102mm	1524mm	3.2mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE