

CFF Tapered Screw-In Plug for A12, A22 and A32K Couplers



FEATURES

Designed for use with the A12, A22 and A32K coupler families

Designed to keep dirt, water and concrete slurry out of the coupler during the concrete pour

Durable mounting plates allow for easy attachment to forms

Color coded for the appropriate coupler size


SPECIFICATIONS

Material: High Density Polyethylene (HDPE);Steel

Table 1/1										
Catalog Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Height (H)	Color				
EL36CFF	36 mm	#11	35M	95 mm	18 mm	Blue				
EL28CFF	28 mm	#9	30M	75 mm	18 mm	Black				
EL22CFF	22 mm	#7		75 mm	18 mm	Blue				
EL32CFF	32 mm	#10		95 mm	18 mm	Yellow				

CatalogNumber	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Height (H)	Color
EL25CFF	25 mm	#8	25M	75 mm	18 mm	Red
EL40CFF	40 mm			95 mm	18 mm	Green
EL50CFF	50 mm			95 mm	18 mm	Black
EL30CFF	30 mm			75 mm	18 mm	White

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY HOFFMAN TRACHTE ERICO ILSCO SCHROFF