

CIPP Tapered Plastic Push-In Plug for A12



FEATURES

Designed for use with the A12 coupler families

Designed to keep dirt and water out of the coupler during transportation and installation

Color coded for the appropriate coupler size

SPECIFICATIONS


Material: Polyethylene

Table 1/1

Catalog Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Height (H)	Color
EL10CIPP	10 mm	#3		15 mm	7 mm	Yellow
EL12CIPP	12 mm	#4	10M	17 mm	7 mm	Red
EL14CIPP	14 mm			19 mm	7 mm	Green
EL16CIPP	16 mm	#5	15M	21 mm	7 mm	Black
EL18CIPP	18 mm			24 mm	7 mm	White
EL20CIPP	20 mm	#6	20M	27 mm	9 mm	Yellow

CatalogNumber	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Height (H)	Color
EL22CIPP	22 mm	#7		29 mm	9 mm	Blue
EL25CIPP	25 mm	#8	25M	32 mm	9 mm	Red
EL28CIPP	28 mm	#9	30M	35 mm	9 mm	Black
EL30CIPP	30 mm			38 mm	9 mm	White
EL32CIPP	32 mm	#10		40 mm	10 mm	Yellow
EL34CIPP	34 mm			42 mm	10 mm	Red
EL36CIPP	36 mm	#11	35M	44 mm	10 mm	Blue
EL38CIPP	38 mm	#12		46 mm	10 mm	White
EL40CIPP	40 mm			48 mm	10 mm	Green
EL43TCIPP	43 mm	#14	45M	54 mm	11 mm	Red
EL50TCIPP	50 mm			62 mm	11 mm	Black
EL57TCIPP	57 mm	#18	55M	69 mm	11 mm	Blue

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE