

nVent LENTON Quick Wedge Replacement Pin



Wedge pins are provided with the purchase of couplers. Replacement wedge pins are made available as a convenience, should any get lost on the jobsite.

FEATURES

Package comes with twenty-six replacement wedge pins and one grommet

Designed to withstand the forces required for assembly

SPECIFICATIONS

Material: Steel

Table 1/2

Catalog Number	Finish	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Length (L)
ML4GPKG26	Mechanical Galvanized	12 mm	#4	10M	13 mm	40mm
ML4PKG26	Plain	12 mm	#4	10M	13 mm	40mm
ML5GPKG26	Mechanical Galvanized	16 mm	#5	15M	13 mm	46mm
ML5PKG26	Plain	16 mm	#5	15M	13 mm	46mm
ML6GPKG26	Mechanical Galvanized	20 mm	#6	20M	16 mm	53mm
ML6PKG26	Plain	20 mm	#6	20M	16 mm	53mm


Table 2/2

Catalog Number	Unit Weight
ML4GPKG26	0.03 kg
ML4PKG26	0.03 kg
ML5GPKG26	0.04 kg
ML5PKG26	0.04 kg
ML6GPKG26	0.06 kg
ML6PKG26	0.06 kg

ADDITIONAL PRODUCT DETAILS

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Quick Wedge Operator's Manual.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE