

# Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking

## Power Utilities

EMC and IP55 Steel Door with lever handle and 4-Point locking.

### FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

### SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Complies With                                             |
|----------------|-------------|---------|--------|------------|------------|-----------------------------------------------------------|
| 21630-760      | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |
| 21630-761      | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |
| 21630-762      | 38 U        | 1800 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |
| 21630-763      | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |
| 21630-764      | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |

| CatalogNumber | Rack Height | Height  | Width  | Color      | Color Code | Complies With                                             |
|---------------|-------------|---------|--------|------------|------------|-----------------------------------------------------------|
| 21630-765     | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |
| 21630-766     | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |
| 21630-767     | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 |

Table 2/2

| Catalog Number | Locking Type    | Material | Product Type | Protection Rating | Type              | Works With  |
|----------------|-----------------|----------|--------------|-------------------|-------------------|-------------|
| 21630-760      | 4-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |
| 21630-761      | 4-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |
| 21630-762      | 4-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |
| 21630-763      | 4-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |
| 21630-764      | 4-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |
| 21630-765      | 4-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |
| 21630-766      | 5-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |
| 21630-767      | 5-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door, Plain | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**