

RIM2-V Valley Panel



nVent RAYCHEM RIM2 valley panels are designed to mount in the roof valleys and provide a heated melt path down the valley and eliminate water ponding in the valley area. It embeds 2 runs of energy efficient self-regulating heating cable which is mechanically protected by a cover panel.

FEATURES

Simple and fast to install

Aesthetically pleasing solution: by concealing the heating cable, complete snow melt along the roof valley

Available in a wide variety of colors

Long term roof deicing solution: by mechanically protecting the heating cable

High performance and reliable solution: for heavy snow load areas

Energy efficient, self-regulating heating cable plus advanced UL and CSA Certified control systems

Reliable during long life: 20 year product warranty available

Maintenance free

SPECIFICATIONS

Heating Capacity: 52 W/m

Cable Type: Self-Regulating

Table 1/1

Catalog Number	Nominal Voltage	Color
F6287-AL-01-1	120 V	Slate Gray
F6287-AL-01-2	240 V	Slate Gray
F6287-AL-02-1	120 V	Stone White

Catalog Number	Nominal Voltage	Color
F6287-AL-02-2	240 V	Stone White
F6287-AL-03-1	120 V	Bone White
F6287-AL-03-2	240 V	Bone White
F6287-AL-04-1	120 V	Almond
F6287-AL-04-2	240 V	Almond
F6287-AL-05-1	120 V	Sandstone
F6287-AL-05-2	240 V	Sandstone
F6287-AL-06-1	120 V	Sierra Tan
F6287-AL-06-2	240 V	Sierra Tan
F6287-AL-07-1	120 V	Teal
F6287-AL-07-2	240 V	Teal
F6287-AL-08-1	120 V	Regal Blue
F6287-AL-08-2	240 V	Regal Blue
F6287-AL-09-1	120 V	Sky Blue
F6287-AL-09-2	240 V	Sky Blue
F6287-AL-10-1	120 V	Sherwood Green
F6287-AL-10-2	240 V	Sherwood Green
F6287-AL-11-1	120 V	Hartford Green

Catalog Number	Nominal Voltage	Color
F6287-AL-11-2	240 V	Hartford Green
F6287-AL-12-1	120 V	Hemlock Green
F6287-AL-12-2	240 V	Hemlock Green
F6287-AL-13-1	120 V	Patina Green
F6287-AL-13-2	240 V	Patina Green
F6287-AL-14-1	120 V	Dark Ivy
F6287-AL-14-2	240 V	Dark Ivy
F6287-AL-15-1	120 V	Brandywine
F6287-AL-15-2	240 V	Brandywine
F6287-AL-16-1	120 V	Regal Red
F6287-AL-16-2	240 V	Regal Red
F6287-AL-17-1	120 V	Colonial Red
F6287-AL-17-2	240 V	Colonial Red
F6287-AL-18-1	120 V	Terra Cotta
F6287-AL-18-2	240 V	Terra Cotta
F6287-AL-19-1	120 V	Dark Bronze
F6287-AL-19-2	240 V	Dark Bronze
F6287-AL-20-1	120 V	Extra Dark Bronze

Catalog Number	Nominal Voltage	Color
F6287-AL-20-2	240 V	Extra Dark Bronze
F6287-AL-21-1	120 V	Mansard Brown
F6287-AL-21-2	240 V	Mansard Brown
F6287-AL-22-1	120 V	Medium Bronze
F6287-AL-22-2	240 V	Medium Bronze
F6287-AL-23-1	120 V	Matte Black
F6287-AL-23-2	240 V	Matte Black
F6287-AL-24-1	120 V	Classic Copper
F6287-AL-24-2	240 V	Classic Copper
F6287-AL-25-1	120 V	Silver Metallic
F6287-AL-25-2	240 V	Silver Metallic
F6287-AL-26-1	120 V	Champagne Metallic
F6287-AL-26-2	240 V	Champagne Metallic
F6287-AL-27-1	120 V	Cityscape
F6287-AL-27-2	240 V	Cityscape
F6287-AL-28-1	120 V	Charcoal Gray
F6287-AL-28-2	240 V	Charcoal Gray
F6287-AL-29-1	120 V	Tropical Patina

Catalog Number	Nominal Voltage	Color
F6287-AL-29-2	240 V	Tropical Patina
F6287-AL-30-1	120 V	Electric Blue
F6287-AL-30-2	240 V	Electric Blue
F6287-AL-31-1	120 V	Award Blue
F6287-AL-31-2	240 V	Award Blue
F6287-AL-32-1	120 V	Granite Green
F6287-AL-32-2	240 V	Granite Green
F6287-CU-70-1	120 V	Copper
F6287-CU-70-2	240 V	Copper

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT