

# Basic PDU, EB0xxx, 400 VAC, 3-PH

Modular, compact PDU. Ultra-Low Profile Design



## FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

## SPECIFICATIONS

Table 1/6

| Catalog Number | Product Family | Type      | Product Type | Socket Type                        | Socket Quantity | Color |
|----------------|----------------|-----------|--------------|------------------------------------|-----------------|-------|
| EB0403         | Enlogic        | Basic PDU | Socket Strip | (36) C13, (6) C19                  | 42              | Black |
| EB0450         | Enlogic        | Basic PDU | Socket Strip | (21) C13/C19                       | 42              | Black |
| EB0811         | Enlogic        | Basic PDU | Socket Strip | (30) C13, (12) C19                 | 42              | Black |
| EB0850         | Enlogic        | Basic PDU | Socket Strip | (24) C13/C15, (24) C13/C15/C19/C21 | 48              | Black |

Table 2/6

| Catalog Number | Circuit Breaker    | Switched Outlets | Circuit Breaker Quantity | Power Rating | Input Cable Length | Input Cable Location |
|----------------|--------------------|------------------|--------------------------|--------------|--------------------|----------------------|
| EB0403         | No Circuit Breaker | No               | 0                        | 11.0 kVA     | 3m                 | Top Feed             |

| CatalogNumber | Circuit Breaker      | Switched Outlets | Circuit Breaker Quantity | Power Rating                                   | Input Cable Length | Input Cable Location |
|---------------|----------------------|------------------|--------------------------|------------------------------------------------|--------------------|----------------------|
| EB0450        | No Circuit Breaker   | No               | 0                        | 11.5 kVA North America, 11.0 kVA International | 1.8m               | Top Feed             |
| EB0811        | 16 A, 1-pole, Hy-Mag | No               | 6                        | 22.0 kVA                                       | 3m                 | Top Feed             |
| EB0850        | 16 A, 1-pole, Hy-Mag | No               | 6                        | 17.3 kVA North America, 22.1 kVA International | 1.8m               | Top Feed             |

Table 3/6

| Catalog Number | Input Voltage | Phase | Nominal Voltage | Max Power Input | On/Off Switch Included | Amperage (Derated Amperage)                   |
|----------------|---------------|-------|-----------------|-----------------|------------------------|-----------------------------------------------|
| EB0403         | 380 – 415V    | 3 PH  | 415V            | 11.0 kVA        | No                     | 16 A                                          |
| EB0450         | 380 – 415V    | 3 PH  | 415V            | 11.5 / 11.0 kVA | No                     | 20 A (16 A) North America, 16 A International |
| EB0811         | 380 – 415V    | 3 PH  | 415V            | 22.0 kVA        | No                     | 32 A                                          |
| EB0850         | 380 – 415V    | 3 PH  | 415V            | 17.3 / 22.1 kVA | No                     | 30 A (24 A) North America, 32 A International |

Table 4/6

| Catalog Number | Output Voltage | Rack Units | Plug Type              | Metering Type | Removable Input Cable | Material |
|----------------|----------------|------------|------------------------|---------------|-----------------------|----------|
| EB0403         | 230VAC         | 0U         | IEC 60309 516P6 (IP44) | None          | No                    | Steel    |
| EB0450         | 208 – 230VAC   | 0U         | IEC 60309 520P6/516P6  | None          | No                    | Steel    |
| EB0811         | 230VAC         | 0U         | IEC 60309 532P6 (IP44) | None          | No                    | Steel    |
| EB0850         | 208 – 230VAC   | 0U         | IEC 60309 530P6/532P6  | None          | No                    | Steel    |

Table 5/6

| Catalog Number | Finish        | Height | Width | Depth | Weight | Package Quantity |
|----------------|---------------|--------|-------|-------|--------|------------------|
| EB0403         | Powder Coated | 1490mm | 52mm  | 53mm  | 6.11kg | 1                |
| EB0450         | Powder Coated | 1490mm | 56mm  | 55mm  | 9.5kg  | 1                |
| EB0811         | Powder Coated | 1750mm | 55mm  | 53mm  | 9.02kg | 1                |
| EB0850         | Powder Coated | 1780mm | 56mm  | 55mm  | 10kg   | 1                |

Table 6/6

| Catalog Number | Quick Ship |
|----------------|------------|
| EB0403         | No         |
| EB0450         | No         |
| EB0811         | No         |
| EB0850         | No         |

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**