


Front Panel With AC Input Module

Front Panel for CompactPCI Systems with mounted Wide Range AC Input Module containing AC Plug, Fuse Holder and EMC Filter.



CERTIFICATIONS



FEATURES

Voltage 110 VAC ... 250 VAC, 50 Hz ... 60 Hz

Front panel for shielding with EMC textile gasket

Max. current 10 A at 40°C

SPECIFICATIONS

Accessory Type: Front panel

Table 1/2

Catalog Number	Material	Front Finish	Rear Finish	Rack Height	Height	Rack Width
----------------	----------	--------------	-------------	-------------	--------	------------

24579-058	Aluminum	Anodized	Conductive	3U	128.4mm	8HP
24579-059	Aluminum	Anodized	Anodized	3U	261.75mm	8HP

Table 2/2

Catalog Number	Width	Depth	Package Quantity	Finish	Quick Ship
24579-058	40.3mm	2.5mm	1	Anodized	No
24579-059	40.3mm	2.5mm	1	Anodized	No

ADDITIONAL PRODUCT DETAILS

EMC profile seals are required to shield the front panels.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE