

# PSU 19" AC/DC Linear Regulator, Dual

Linear regulator for application which only allows a very low noise level at the outputs.



## CERTIFICATIONS



## FEATURES

2 output voltages, galvanically separated

High control accuracy, low residual ripple and very low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

## SPECIFICATIONS

Table 1/3

Catalog Number	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-018	19" Linear Regulator	230V	12W	2	15V	0.4A
13105-017	19" Linear Regulator	230V	10W	2	12V	0.4A
13105-022	19" Linear Regulator	230V	24W	2	12V	1A

CatalogNumber	Type	Input Voltage AC	Power	Number of OutputVoltages	Voltage 1	Current 1
13105-023	19" Linear Regulator	230V	30W	2	15V	1A
13105-029	19" Linear Regulator	230V	58W	2	24V	1.2A
13105-028	19" Linear Regulator	230V	45W	2	15V	1.5A
13105-021	19" Linear Regulator	230V	14W	2	5V	1.4A
13105-027	19" Linear Regulator	230V	36W	2	12V	1.5A

Table 2/3

Catalog Number	Voltage 2	Current 2	Rack Height	Rack Width	Depth	Package Quantity
13105-018	15V	0.4A	3U	6HP	171.93mm	1
13105-017	12V	0.4A	3U	6HP	171.93mm	1
13105-022	12V	1A	3U	10HP	171.93mm	1
13105-023	15V	1A	3U	10HP	171.93mm	1
13105-029	24V	1.2A	3U	14HP	171.93mm	1
13105-028	15V	1.5A	3U	14HP	171.93mm	1
13105-021	5V	1.4A	3U	10HP	171.93mm	1
13105-027	12V	1.5A	3U	14HP	171.93mm	1

Table 3/3

Catalog Number	Certifications	Quick Ship
13105-018	EN 62368-1, RoHS, CE	No
13105-017	EN 62368-1, RoHS, CE	No

Catalog Number	Certifications	Quick Ship
13105-022	CE, RoHS	No
13105-023	CE, RoHS	No
13105-029	CE, RoHS	No
13105-028	RoHS, CE	No
13105-021	RoHS, CE	No
13105-027	RoHS, CE	No

## ADDITIONAL PRODUCT DETAILS

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**