

PSU 19" AC/DC Maxpower 180 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

CERTIFICATIONS



FEATURES

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active Power Factor Correction (PFC)

1 output voltage

Signalling: Output voltage OK

Efficiency up to 87 %

Integrated active decoupling for redundancy operation

Active Current Share Bus (CSB)

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-152	19" Switched-Mode	90 – 264V	165W	1	15V	11A
13100-151	19" Switched-Mode	90 – 264V	156W	1	12V	13A

CatalogNumber	Type	Input Voltage AC	Power	Number of OutputVoltages	Voltage 1	Current 1
13100-150	19" Switched- Mode	90 – 264V	150W	1	5V	30A
13100-153	19" Switched- Mode	90 – 264V	168W	1	24V	7A

Table 2/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
13100-152	3U	8HP	1	No
13100-151	3U	8HP	1	No
13100-150	3U	8HP	1	No
13100-153	3U	8HP	1	No

ADDITIONAL PRODUCT DETAILS

Please order front panel separately.

Output data for mains voltage > 190 VAC, TA = 0 ... 50 °C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE