

# PSU 19" AC/DC Slimpower Pro, 31 .. 46 W



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

## **FEATURES**

Wide input voltage range 85 ... 253 VAC and 120 ... 358 VDC

1 output voltage with low interferences (low ripple < 25 mVPP)

Signalling: Output voltage OK

Wdith only 3 HP (15,24 mm)

Integrated decoupling diode for redundancy operation (can be activated)

Passive Current Share Bus

#### **SPECIFICATIONS**

Table 1/2									
Catalog Number	Туре	Input Voltage	Input Voltage DC	Power	Number of Output Voltages	Voltage 1			
13100-178	19" Switched- Mode	85 – 253V	120 – 358V	42W	1	15V			
13100-177	19" Switched- Mode	85 – 253V	120 – 358V	42W	1	12V			
13100-176	19" Switched- Mode	85 – 253V	120 – 358V	31W	1	5V			
13100-179	19" Switched- Mode	85 – 253V	120 – 358V	46W	1	24V			

Table 2/2									
Catalog Number	Current 1	Rack Height	Rack Width	Package Quantity	Quick Ship				
13100-178	2.8A	3U	ЗНР	1	No				
13100-177	3.5A	3U	ЗНР	1	No				
13100-176	6.2A	3U	ЗНР	1	No				
13100-179	1.9A	3U	3HP	1	No				

### ADDITIONAL PRODUCT DETAILS

Front panel included in delivery

Output data at Ta= -25 ... 50 °C.

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

## Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

## Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE