

Socket Strip, UTE



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with UTE outlets.

CERTIFICATIONS



FEATURES

230 V, 16 A

In accordance with NFC 61-303

Socket strip with UTE sockets

Mounting height 1 U

Horizontal or vertical mounting

Connecting cable 2 m, with SCHUKO/UTE plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFICATIONS

Material: Aluminum; Polyamide

Color: Grey

Product Type: Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
----------------	-------------	-----------------	------------------	------------	----------	------------------

60110-220	UTE	4	No	230V		1
60110-221	UTE	9	No	230V		1
60110-225	UTE	8	Yes	230V		1
60110-267	UTE	6	No	230V	Transient Protection, Mains Suppression Filter	1
60110-227	UTE	8	No	230V	Transient Protection	1
60110-229	UTE	7	No	230V	Mains Suppression Filter	1
60110-222	UTE	12	No	230V		1
60110-223	UTE	15	No	230V		1
60110-224	UTE	19	No	230V		1
60110-226	UTE	12	Yes	230V		1
60110-228	UTE	6	No	230V	Overcurrent Protection	1
60110-230	UTE	6	No	230V	Fault Current Protection	1
60110-231	UTE	6	No	230V	Fault Current Protection, Overcurrent Protection	1

Table 2/2

Catalog Number	Depth	Finish	Length	Quick Ship
60110-220	44mm	Anodized	210mm	No
60110-221	44mm	Anodized	438.5mm	No
60110-225	44mm	Anodized	438.5mm	No

Catalog Number	Depth	Finish	Length	Quick Ship
60110-267	44mm	Anodized	438.5mm	No
60110-227	44mm	Anodized	438.5mm	No
60110-229	44mm	Anodized	438.5mm	No
60110-222	44mm	Anodized	947.5mm	No
60110-223	44mm	Anodized	1202mm	No
60110-224	44mm	Anodized	1753mm	No
60110-226	44mm	Anodized	947.5mm	No
60110-228	75mm	Anodized	438.5mm	No
60110-230	88mm	Anodized	438.5mm	No
60110-231	88mm	Anodized	438.5mm	No

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE