

Improved nVent CADDY Cat HP J-Hook Mod Clip with Pedestal Clamp



Improved nVent CADDY Cat HP Mod Clip J-Hook with Pedestal Clamp simplifies installation to pedestals under raised floors. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

CERTIFICATIONS





FEATURES


Listed for use with flexible conduit, cable, or tubing

Requires no screws, rivets or special tools for assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY

SPECIFICATIONS

| Table 1/1 | | | | | |
|----------------|----------------|---|---------------------|------------------------------|-------------|
| Catalog Number | Article Number | Finish | Material | Pedestal Size | Static Load |
| CATHPMCD1B | 186083 | Electrogalvanized, nVent CADDY Armour | Steel, Spring Steel | 19 mm Square, 25 mm Round | 70N |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.