

nVent ERIFLEX Flexbus HCBC Plate with PE Connection



CERTIFICATIONS



FEATURES

Rigid tinned copper part provides strong electrical contact to maintain braid expansion during compression

HCBC Plate allows Flexbus Conductor insulation to overlap the connection palm

HCBC Plate with PE connection allows conductor to be added to interconnect neutral and ground/earth

Tinned copper allows for copper or aluminum conductor connections

Installs quickly and easily

RoHS compliant

SPECIFICATIONS

Material: Copper

Finish: Tinned

Table 1/2

Catalog Number	Article Number	A	B	C	D	E
----------------	----------------	---	---	---	---	---

FLEXPLATE50PE	508182	65 mm	100 mm	45 mm	41 mm	70 mm
FLEXPLATE100PE	508183	115 mm	100 mm	45 mm	51 mm	70 mm


Table 2/2

Catalog Number	Article Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Thickness (T)	Conductor Size	Unit Weight
FLEXPLATE50PE	508182	10.5 mm	14.5 mm	5 mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²	0.49 kg
FLEXPLATE100PE	508183	12.5 mm	18.5 mm	5 mm	960 mm ² , 1280 mm ² , 1810 mm ²	0.71 kg

ADDITIONAL PRODUCT DETAILS

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE