

Window Door, ADC



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: To replace the standard door, it provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s).

Material: 1.2 mm mild steel / 1.5 mm for enclosures with a height or width of 500 mm or greater / 2 mm for enclosures with a height or width of 800 mm or greater and 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, 13, IK 07.

Pack quantity: 1 door.

SPECIFICATIONS

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

| Catalog Number | Height | Width | Depth | Thickness | Latch Quantity | Window Size |
|----------------|--------|-------|-------|-----------|----------------|--------------|
| ADC03025R5 | 300mm | 250mm | 15mm | 1.2mm | 1 | 159 x 93mm |
| ADC03030R5 | 300mm | 300mm | 15mm | 1.2mm | 1 | 159 x 143mm |
| ADC04030R5 | 400mm | 300mm | 15mm | 1.2mm | 1 | 259 x 143mm |
| ADC04040R5 | 400mm | 400mm | 15mm | 1.2mm | 1 | 259 x 243mm |
| ADC05030R5 | 500mm | 300mm | 15mm | 1.5mm | 1 | 359 x 143mm |
| ADC05040R5 | 500mm | 400mm | 15mm | 1.5mm | 1 | 359 x 243mm |
| ADC06040R5 | 600mm | 400mm | 15mm | 1.5mm | 2 | 459 x 243mm |
| ADC06050R5 | 600mm | 500mm | 15mm | 1.5mm | 2 | 459 x 343mm |
| ADC06060R5 | 600mm | 600mm | 15mm | 1.5mm | 2 | 459 x 443mm |
| ADC07050R5 | 700mm | 500mm | 15mm | 1.5mm | 2 | 559 x 343mm |
| ADC08060R5 | 800mm | 600mm | 15mm | 2mm | 2 | 659 x 443mm |
| ADC10060R5 | 1000mm | 600mm | 15mm | 2mm | 1 | 859 x 427mm |
| ADC10080R5 | 1000mm | 800mm | 15mm | 2mm | 1 | 859 x 627mm |
| ADC12060R5 | 1200mm | 600mm | 15mm | 2mm | 1 | 1059 x 427mm |
| ADC12080R5 | 1200mm | 800mm | 15mm | 2mm | 1 | 1059 x 627mm |

ADDITIONAL PRODUCT DETAILS

* 3 point espagnolette locking. Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE