

# Horizontal and Vertical Packing



The horizontal and vertical packing materials seal the gaps that can exist between the sleeve and reinforcing steel bar. The packing materials help ensure the molten filler material remains in the sleeve until it solidifies.

## FEATURES

Heat-resistant

Pliable material forms to the reinforcing steel contours

Helps prevent leaking of molten filler material

## SPECIFICATIONS

Table 1/1


| Catalog Number | Diameter (Ø) | Length (L) | Unit Weight |
|----------------|--------------|------------|-------------|
| RBS35473.5     | 13 mm        | 89mm       | 0 kg        |
| RBS354710      | 13 mm        | 250mm      | 0.01 kg     |
| RBS354711      | 13 mm        | 279mm      | 0.01 kg     |
| RBS354712      | 13 mm        | 305mm      | 0.01 kg     |
| RBS354714      | 13 mm        | 356mm      | 0.01 kg     |
| RBS354715      | 13 mm        | 381mm      | 0.01 kg     |
| RBS354716      | 13 mm        | 406mm      | 0.01 kg     |

| Catalog Number | Diameter (Ø) | Length (L) | Unit Weight |
|----------------|--------------|------------|-------------|
| RBS354718      | 13 mm        | 457mm      | 0.01 kg     |
| RBS354720      | 13 mm        | 508mm      | 0.01 kg     |
| RBS35474       | 13 mm        | 102mm      | 0.01 kg     |
| RBS35475       | 13 mm        | 127mm      | 0.01 kg     |
| RBS35475.5     | 13 mm        | 140mm      | 0.01 kg     |
| RBS35476       | 13 mm        | 152mm      | 0.01 kg     |
| RBS35477       | 13 mm        | 178mm      | 0.01 kg     |
| RBS35478       | 13 mm        | 203mm      | 0.01 kg     |
| RBS35479       | 13 mm        | 229mm      | 0.01 kg     |
| RBS354725      | 13 mm        | 635mm      | 0.02 kg     |

## ADDITIONAL PRODUCT DETAILS

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**