

# 19" Pusher Fan, 2 U, Axial

## Power Utilities

Fan tray with integrated pusher fan.



### CERTIFICATIONS



### FEATURES

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

### SPECIFICATIONS

Table 1/1

| Catalog Number | Input Voltage AC | Input Voltage DC |
|----------------|------------------|------------------|
| 10713-518      | 230 V min        |                  |
| 10713-520      | 115 V min        |                  |

| Catalog Number | Input Voltage AC | Input Voltage DC |
|----------------|------------------|------------------|
| 10713-526      | 230 V min        |                  |
| 10713-534      | 230 V min        |                  |
| 10713-536      | 115 V min        |                  |
| 10713-529      |                  | 24 V min         |
| 10713-537      |                  | 24 V min         |
| 19713-540      |                  |                  |

### ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE