

CABS Busbar Support Kit

Power Utilities



CERTIFICATIONS



FEATURES

For all busbar types

Improve bending resistance by interlocking or stacking two profiles

Quick and easy to install

Halogen free insulators

RoHS compliant

SPECIFICATIONS


Table 1/3

Catalog Number	Article Number	Typical Application Current Rating	Max Working Voltage, IEC (Ui)	Working Temperature	Busbars per Phase	Busbar Width
CABS4-5TN-400	549310	400 – 4,500 A	1,000 VAC, 1,500 VDC	-40 to 130 °C	1 – 4	30 – 125 mm

Table 2/3						
Catalog Number	Article Number	Busbar Thickness	Width (W)	A	B	C
CABS4-5TN-400	549310	5 mm	350 mm	300 mm	75 mm	325 mm

Table 3/3		
Catalog Number	Article Number	Unit Weight
CABS4-5TN-400	549310	0.800 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE