


# 19" Fan Unit, 1 U

Fan Unit for installation into a 1U space within the Cabinet.



## CERTIFICATIONS



## FEATURES

Mechanical strain relief for mains cables

Can be adapted to sub racks

Contact protection in accordance with DIN EN ISO 13857

## SPECIFICATIONS

Table 1/1

| Catalog Number | Input Voltage AC | Input Voltage DC | Package Quantity | Finish                         | Material        | Quick Ship |
|----------------|------------------|------------------|------------------|--------------------------------|-----------------|------------|
| 10713-100      | 230V             |                  | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |
| 10713-107      |                  | 24V min          | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |
| 10713-106      | 115V             |                  | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |

| CatalogNumber | Input Voltage AC | Input Voltage DC | Package Quantity | Finish                         | Material        | Quick Ship |
|---------------|------------------|------------------|------------------|--------------------------------|-----------------|------------|
| 10713-104     | 230V             |                  | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |
| 10713-102     | 115V             |                  | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |
| 10713-103     |                  | 24V min          | 1                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |

## ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

Wide-range input voltage (86 ... 264 VAC) available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**