nVent | SCHROFF

We connect and protect

Door Stopper Kit for Varistar CP

CATALOG NUMBER

24630-164

Designed for use with Varistar CP enclosures to secure the door in 90° or 120° standard open positions. It can be used in rugged environments and applications like Seismic and MIL. This door stop kit is ideal for use in applications that require the kind of corrosion protection as the components are Aluminum and steel with Zinc plating.

FEATURES

- Designed to be mounted at the bottom of door
- Can be installed on either left- or right-hinged doors
- The user manual will give standard positions for 90° and 120° angles
- Anchor point is in front of the 19 inch uprights and hence there is no loss of rack unit at bottom
- Does not work with glass doors

PRODUCT ATTRIBUTES

- Product Type: Assembly Kit
- Works With: Varistar CP
- Material: Aluminum; Steel
- Finish: Zinc Plated
- Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.