


Horizontal Rail, Rear, Type L-MZ, Light, With Z-Rail, 84 HP

CATALOG NUMBER

34560-884



Combinations of horizontal rails and side panels

	A° = can be combined.	$A^{\circ} + B^{\circ}$ = combination: not recommended	$A^{\circ} + C^{\circ}$ = combination: not recommended	$A^{\circ} + D^{\circ}$ = combination: not recommended
light = L		-	+	+
heavy = H		+	rework for flange (see combination)	rework for flange and connection for heavy
light + L		rework for light	rework for flange	-
heavy + H		+	+	-
light + L		-	-	-
heavy + H		+	+	+
light + L		+	+	-
heavy + H		+	+	+
light + L		-	-	-
heavy + H		+	+	+
light + L		+	+	-
heavy + H		+	+	+
light + L		-	-	-
heavy + H		+	+	+
light + L		+	+	-
heavy + H		+	+	+

The horizontal rail, type light with MZ enables the use of DIN connectors. The connectors are in accordance with EN 60603-2.

CERTIFICATIONS



FEATURES

For directly mounting connectors complying with EN 60603 (DIN 41612)

With Z-rail for low mechanical load (L-MZ)

Aluminum extrusion, anodized finish, conductive contact surface

PRODUCT ATTRIBUTES

Rack Width: 84HP

Package Quantity: 1

Finish: Anodized

Length: 431.8mm

Material: Aluminum

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Type: Light, MZ

Works With: Subracks; Cases

Net Weight: 0.14kg

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE