

Eye Screw



FEATURES

Designed to accept nVent CADDY Speed Link wire rope or hook

SPECIFICATIONS


Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Article Number	Screw Diameter (Sc)	Screw Length (L)	Hole Size (HS)	Length (L)
SLEB250		0.25	25mm	7.2 mm	44mm
SLEB375		0.375	45.7mm	7.2 mm	63.5mm
SLEBM6	195854	6	20mm	7.2 mm	37.5mm
SLEBM8	195856	8	25mm	8.5 mm	50mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

