

Push-In Metal Deck Conduit Clamp



FEATURES

Provides spacing between conduit and deck surface

Easily attached with screw gun or power tool

Permits conduit to be laid out and then attached

Eliminates need for offset bending conduit

SPECIFICATIONS

Finish: nVent CADDY Armour;Pregalvanized

Material: Spring Steel;Steel

Table 1/1

Catalog Number	Outer Diameter	Hole Size
AOL8P	12.7 mm	6.4 mm
AOL12P	19.1 mm	6.4 mm
AOL16P	25.4 mm	6.4 mm

ADDITIONAL PRODUCT DETAILS

No load rating, for positioning only.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

