

# Cable to Web of Rail Mold Only, Signal, Field-made Bond Terminal Style, 50 mm<sup>2</sup> Solid, Right Hand

## Data Solutions

### CATALOG NUMBER

---

**SBWW6RH**



### FEATURES

---

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

### PRODUCT ATTRIBUTES

---

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: Field-made

Conductor Size: 50 mm<sup>2</sup> Solid

Conductor Outer Diameter, Nominal: 8mm

Welder Style: T21

Orientation: Right Hand

Mold Only: Yes

Welding Material: SB32 or SB25PLUSF80, Sold Separately

Handle Clamp: C105B, Sold Separately

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**