

# Air Terminal Base, Vertical Mount with Offset, Imperial Thread



## CERTIFICATIONS



## FEATURES

For use on vertical surfaces

Offset provides clearance for overhang of wall cap or cover

Accommodates vertical or horizontal cable runs

For positive bolt tension cable clamping

## SPECIFICATIONS

**Conductor Size, UL:** Class 1 - Class 2 (4/0 Max)


Table 1/2

| Catalog Number | Material | Finish | Thread Size (TS) | Depth (D) | Height (H) | Width (W) |
|----------------|----------|--------|------------------|-----------|------------|-----------|
| LPA31958       | Aluminum | Bare   | 5/8" UNC         | 59.53mm   | 79.38 mm   | 79.38 mm  |
| LPC31912       | Copper   | Bare   | 1/2" UNC         | 59.53mm   | 79.38 mm   | 79.38 mm  |

| CatalogNumber | Material | Finish | Thread Size (TS) | Depth (D) | Height (H) | Width (W) |
|---------------|----------|--------|------------------|-----------|------------|-----------|
| LPC31938      | Copper   | Bare   | 3/8" UNC         | 59.53mm   | 79.38 mm   | 79.38 mm  |
| LPC31958      | Copper   | Bare   | 5/8" UNC         | 59.53mm   | 79.38 mm   | 79.38 mm  |
| LPC319L12     | Copper   | Tinned | 1/2" UNC         | 59.53mm   | 79.38 mm   | 79.38 mm  |
| LPC319L38     | Copper   | Tinned | 3/8" UNC         | 59.53mm   | 79.38 mm   | 79.38 mm  |
| LPC319L58     | Copper   | Tinned | 5/8" UNC         | 59.53mm   | 79.38 mm   | 79.38 mm  |

| Table 2/2      |                |         |             |
|----------------|----------------|---------|-------------|
| Catalog Number | Hole Size (HS) | A       | Unit Weight |
| LPA31958       | 12.7 mm        | 38.1 mm | 0.13 kg     |
| LPC31912       | 12.7 mm        | 38.1 mm | 0.38 kg     |
| LPC31938       | 12.7 mm        | 38.1 mm | 0.38 kg     |
| LPC31958       | 12.7 mm        | 38.1 mm | 0.38 kg     |
| LPC319L12      | 12.7 mm        | 38.1 mm | 0.38 kg     |
| LPC319L38      | 12.7 mm        | 38.1 mm | 0.38 kg     |
| LPC319L58      | 12.7 mm        | 38.1 mm | 0.38 kg     |

### DIAGRAMS



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**⚠ WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**