

# Galvanized Ground Rod, Pointed



## CERTIFICATIONS



## FEATURES

Meets ANSI®/NEMA® GR1

Zinc-coated exteriors are hot-dip galvanized for solid protection against corrosion, in accordance with ASTM® specification A123

Surfaces are rigidly inspected to eliminate seams, slivers and other defects

## SPECIFICATIONS

**Finish:** Hot-Dip Galvanized

**Material:** Steel

**Tensile Strength:** 552 MPa Min

Table 1/1

Catalog Number	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Length (L)	Unit Weight	UPC Label	Certifications
811350	1/2"	12.95 mm	1.52mm	1.5 kg	No	

CatalogNumber	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Length (L)	Unit Weight	UPC Label	Certifications
811360	1/2"	12.95 mm	1.83mm	1.8 kg	No	
811380	1/2"	12.95 mm	2.44mm	2.4 kg	No	
815800	5/8"	16 mm	3.05mm	4.8 kg	No	CSA-US, CSA
815850	5/8"	16 mm	1.52mm	2.4 kg	No	
815860	5/8"	16 mm	1.83mm	2.9 kg	No	
815880	5/8"	16 mm	2.44mm	3.8 kg	No	RUS
813400	3/4"	18.54 mm	3.05mm	6.3 kg	No	UL
813480	3/4"	18.54 mm	2.44mm	5.1 kg	No	RUS, UL
814400	1"	25.65 mm	3.05mm	12.3 kg	No	CSA, CSA-US

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**