


Theft-Deterrent Grounding Busbar, Flange Mount Assembly



CERTIFICATIONS



FEATURES

Mounts to a typical structural beam flange on a telecom tower without cutting or drilling the flange

Accepts standard telecommunication grounding lugs (lugs not included)

Includes 14 Standard Spacers (TDSGAS)

SPECIFICATIONS

Table 1/2


Catalog Number	Material	Finish	Spacer Thickness	Length 1 (L1)	Length 2 (L2)	Depth (D)
TDSGABC14	Copper, Stainless Steel 18-8 (EN 1.4305), Nylon	Tinned	6.4mm	266 mm	101.6 mm	54.1mm

Table 2/2

Catalog Number	Height (H)	A	Flange Thickness (FT)	Thread Size 1 (TS1)	Thread Size 2 (TS2)	Thread Size 3 (TS3)
----------------	------------	---	-----------------------	---------------------	---------------------	---------------------

TDSGABC14	69 mm	25.4 mm	6.4 - 25.4 mm	3/8" UNC	5/16" UNC	5/16" UNC
-----------	-------	---------	---------------	----------	-----------	-----------

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE