We connect and protect

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

CATALOG NUMBER

34566-284



The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness
- Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

- Product Type: Horizontal Rail
- Product Family: EuropacPRO
- Type: Rugged, KD
- Rack Width: 84 HP
- Length: 431.8 mm

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.