


EuropacPRO 19" Subrack Kit for Power Distribution Module, Unshielded

Power Utilities



For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted.

CERTIFICATIONS



FEATURES

For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted

Modular frame to accept e.g. power distribution modules

Internal and external dimensions in accordance with the IEC 60297-3-101 and IEEE 1101.1 standards

Aluminium side panels

Horizontal rails type "light"

IEEE 1101.1 compatible

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Rack Height	Rack Width	Depth	For Mounting	EMC Shielding
----------------	--------------	-------------	------------	-------	--------------	---------------

24563-100	Subrack/Chassis	3 U	84 HP	115 mm	Power Distribution Module	No
-----------	-----------------	-----	-------	--------	---------------------------	----

Table 2/2

Catalog Number	Static Load	Handle Included	Mounting	Complies With	Package Quantity
24563-100	2.5 kgf	No	Rack	IEC 60297-3-103	1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE