

Plug-In Unit Kit for FMC, Chromated, Shielded (Textile) With Handle



The FMC bezel are in accordance with Vita 57.1 specification. Covers the cut out in the overall front panel.

CERTIFICATIONS



FEATURES

In accordance with Vita 57.1 specification

For single 69.0 x 76.5 mm or double 139.0 x 76.5 mm modules

AI-Profile plug-in unit with IEL handle

SPECIFICATIONS

Rack Width:	4HP
Material:	Aluminum
Finish:	Anodized; Passivated
Product Type:	Front Panel

Type: Front Panel with Handle (PIU)

EMC Shielding: Yes

Table 1/2

Catalog Number	Rack Height	Package Quantity	Handle Type	Mounting	Front Finish	Rear Finish
20836-253	3U	1	IEL	Screw-on Front	Anodized	Conductive
20836-254	6U	1	IEL	Screw-on Front	Anodized	Conductive

Table 2/2

Catalog Number	Treated Edges	Complies With	Height	Width	Quick Ship
20836-253	No	FMC Mezzanine, Vita 57.1	128.4mm	20mm	No
20836-254	No	FMC Mezzanine, Vita 57.1	261.8mm	20mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE