

# Socket Strip With 2 Supply Cable, 3-Phase

Modular, compact PDU with two power cord inputs that can be connected to an A and B power feed. Space saving design in one chassis.



## CERTIFICATIONS



## FEATURES

Horizontal and vertical assembly possible

Two connector cables (halved in direction of length), 3 m (with open end), 2 x 3 phase, 400 VAC (red, black, white area)

Socket strips can be rotated in all directions (in 90° increments) during installation

Mounting height 1 U

## SPECIFICATIONS

|                      |                     |
|----------------------|---------------------|
| <b>Length:</b>       | 1848,5mm            |
| <b>Material:</b>     | Aluminum; Polyamide |
| <b>Color:</b>        | Grey; Black; Red    |
| <b>Product Type:</b> | Socket Strip        |

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Package Quantity | Depth |
|----------------|-------------|-----------------|------------------|------------|------------------|-------|
| 60110-287      | IEC C13     | 48              | No               | 400V       | 1                | 44mm  |

| CatalogNumber | Socket Type     | SocketQuantity | Switched Outlets | Voltage AC | Package Quantity | Depth |
|---------------|-----------------|----------------|------------------|------------|------------------|-------|
| 60110-286     | IEC C13, SCHUKO | 36             | No               | 400V       | 1                | 44mm  |

Table 2/2

| Catalog Number | Finish   | Height | Quick Ship |
|----------------|----------|--------|------------|
| 60110-287      | Anodized | 44mm   | No         |
| 60110-286      | Anodized | 44mm   | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**