

Rail Head Track Circuit Single Shunt, T-Handle, Orange, 7,620 mm, 2 Contact Points

CATALOG NUMBER

SBB2721WS300



FEATURES

Easy-to-carry assembly that can be used on most common rail types

Two shunt assemblies are available: "Hard" zero ohm or 0.06 ohm

No resistor to fail: Product is pre-engineered to provide permanent 0.06 ohm shunting

Tested to assure reliability of 0.06 ohm shunt

Bright orange insulation on "Hard" shunt for high visibility and easy identification

Cable welded to terminal clamp

Hardened contact points on clamps bite through rust and scale

Unique design assures positive contact and firm grip

T-shaped handle allows quick and easy tightening by hand

PRODUCT ATTRIBUTES

Material: Steel;Cadmium Bronze;Polyvinylchloride

Color: Orange

Length (L): 7620mm

Width (W): 95.25 mm

Height (H): 25.4 mm

Rail Head Size (RHS): 76.2 mm Max

Shunt: Hard (Zero Ohm)


Conductor Size: 3/16" Bondstrand

Number of Contact Points: 2

ADDITIONAL PRODUCT DETAILS

In order to meet the electrical requirements of 0.06 Ohms, the manufactured length may be longer than the indicated length.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including cadmium and vinyl chloride, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE