

Industrial Stack Cross-Run Connector



CERTIFICATIONS



FEATURES

Cast cross-run clamp for connecting down conductors

Can be used as a straight connection clamp by rotating the top plate

SPECIFICATIONS

Material: Brass

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)


Table 1/1

Catalog Number	Finish	Depth (D)	Height (H)	Width (W)	Unit Weight	Certifications
LPC448	Bare	73.35mm	34.3 mm	73.35 mm	0.48 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPLC448	Lead Covered	73.35mm	34.3 mm	73.35 mm	1.21 kg	

ADDITIONAL PRODUCT DETAILS

Where applicable, lead covering thickness is a minimum of 1/16" (1.59 mm) and is not included in the stated dimensions.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE