

Plug Bond Track Connector, Signal Kit



FEATURES

Used when bondstrand is being utilized for track connections

Hammered into a 3/8" (9.5 mm) diameter hole drilled through the rail web and driven from the same side the hole was drilled

SPECIFICATIONS

Table 1/1

Catalog Number	Conductor Size	Connector Conductor Size	Length (L)	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Depth (D)
SBK060	3/16" Bondstrand	#6 Solid	120.7mm	4.8 mm	10.5 mm	31.75mm

ADDITIONAL PRODUCT DETAILS

Kit includes: (1) tube of plug bond grease, (2) plug bond track connectors, signal, 15' (0.3 m) of orange Insulated 3/16" bondstrand, (2) tinned copper compression sleeves, (4) wooden tie conductor fixing staples, (2) hammer-on rail clips, one conductor perpendicular to foot, (2) 9" (229 mm) long heat shrink tubing, and (2) 18" (457 mm) long polyethylene bootleg riser with hole.

Plug Bond Grease (T369) recommended when installing.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE