

Rail Joint Bond, Signal, Tab Style



The nVent ERICO Cadweld joint bonds are intended to be welded to the head of the rail profile within the confines of the joint bar. To ensure connection integrity, the attachment shall be made using nVent ERICO Cadweld welding material.

FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Easy installation, with minimum installer training required

Simple and highly-portable installation equipment

Equally usable on old, worn, or new rails

Highly durable

SPECIFICATIONS

Rail Type: 85 lb to 141 lb T-Rail Sections

Finish: Bare;Tinned


Material: Cadmium Bronze;Copper

Table 1/1

Catalog Number	Bond Terminal Style	Conductor Size	Bond Length	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SB20108B	Tab	3/16" Bondstrand	247.65mm	198.4 mm	19.05 mm	4.8 mm
SB20112B	Tab	3/16" Bondstrand	165.1mm	115.9 mm	19.05 mm	4.8 mm
SB20128B	Tab, Head Free	3/16" Bondstrand	190.5mm	144.5 mm	19.05 mm	4.8 mm

CatalogNumber	Bond Terminal Style	Conductor Size	Bond Length	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SB20136B	Tab	3/16" Bondstrand	190.5mm	144.5 mm	19.05 mm	4.8 mm
SB20104B	Tab	3/16" Bondstrand	165.1mm	115.9 mm	19.05 mm	4.8 mm
SB20175B	Tab	5/16" Bondstrand	177.8mm	146.1 mm	25.4 mm	7.9 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE