


Universal Conductor Clip, Plastic



FEATURES

Secures either round or tape conductors

Can be mechanically fastened to a surface or attached to plastic adhesive bases

UV resistant, designed and tested for outdoor use

Material UV performance meets the UL® 746C standard

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Temperature	Conductor Size	Tape Size	Depth (D)
PDCUC	711352	Polycarbonate	-20 to 120 °C	8 mm ² Stranded, 8 mm ² Solid	25 x 3 mm, 26 x 2 mm	20mm

Table 2/2

Catalog Number	Article Number	Width (W)	Hole Size (HS)	Static Load	Unit Weight
PDCUC	711352	35.9 mm	6.8 mm	1000N	0.01 kg

ADDITIONAL PRODUCT DETAILS

When using the adhesive base, recommended installation temperatures are limited to 15 °C to 38 °C (59 °F to 100 °F).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE