




AFBS - B600	5049 71	Steel, Alum inum, Glass Fibre Reinf orce d Polya mide	1,000 VAC, 1,500 VDC	-40 to 130 °C	IEC@ 6043 9.1, IEC@ 6143 9.1, IEC@ 6069 5-2- 11 (Glo w Wire Test 960 °C)	UL@ 94V- 0	30 – 80 mm	5 – 10 mm	549 – 749 mm	70 mm	507 mm	61 – 176 mm	525 – 725 mm	M8	2.200 kg
-------------------	------------	--	-------------------------------	------------------------	---	------------------	------------------	-----------------	-----------------------	----------	-----------	-------------------	-----------------------	----	-------------

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**