

Plain Doors, DN-NC



FEATURES

Plain mild steel door to replace the rear panel on floor standing enclosures

It allows easy access from the rear of the enclosure

Access to the rear of the equipment installed in the front, or increase the mounting area using back to back mounting plates

SPECIFICATIONS

Thickness: 2mm
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

| Catalog Number | Height | Width | Depth | Material | Quick Ship |
|----------------|--------|-------|-------|------------|------------|
| DNNCD1805LR5 | 1782mm | 493mm | 17mm | Mild Steel | No |
| DNNCD1805RR5 | 1782mm | 493mm | 17mm | Mild Steel | No |
| DNNCD1806LR5 | 1782mm | 593mm | 17mm | Mild Steel | No |
| DNNCD1806RR5 | 1782mm | 593mm | 17mm | Mild Steel | No |
| DNNCD2005LR5 | 1982mm | 493mm | 17mm | Mild Steel | No |
| DNNCD2005RR5 | 1982mm | 493mm | 17mm | Mild Steel | No |
| DNNCD2006LR5 | 1982mm | 593mm | 17mm | Mild Steel | No |
| DNNCD2006RR5 | 1982mm | 593mm | 17mm | Mild Steel | No |
| DNNCD2206LR5 | 2182mm | 593mm | 17mm | Mild Steel | No |
| DNNCD2206RR5 | 2182mm | 593mm | 17mm | Mild Steel | No |
| DNNCS1806R5 | 1782mm | 593mm | 17mm | Mild Steel | No |
| DNNCS1808R5 | 1782mm | 792mm | 17mm | Mild Steel | No |
| DNNCS2006R5 | 1982mm | 593mm | 17mm | Mild Steel | No |
| DNNCS2008R5 | 1982mm | 792mm | 17mm | Mild Steel | No |
| DNNCS2208R5 | 2182mm | 792mm | 17mm | Mild Steel | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE